

Technical Data Sheet

Ultracur3D[®] DMD 1005

Daylight | Dental Model | Beige

General Properties	Norm	Typical Values
Appearance	-	Beige
Viscosity, 30 °C	Cone/Plate Rheometer ¹	110 mPas
Viscosity, 50 °C	Cone/Plate Rheometer ¹	40 mPas
Density (printed part)	ASTM D792	1.5 g/cm ³

Tensile Properties	Norm (5 mm/min)	Typical Values
E Modulus	ASTM D638	2710 MPa
Ultimate Tensile Strength	ASTM D638	60 MPa
Elongation at Break	ASTM D638	4 %

Flexural Properties	Norm	Typical Values
Flexural Modulus	ASTM D790	2400 MPa
Flexural Strength	ASTM D790	85 MPa

Impact Properties	Norm	Typical Values
Unnotched Izod (Machined), 23 °C	ASTM D256	10 J/m
Notched Izod (Machined), 23 °C	ASTM D256	1.6 J/m
Charpy notched, 23 °C	ISO 179-1	1.1 kJ/m ²

Thermal Properties	Norm	Typical Values
HDT at 0.45 MPa	ASTM D648	93 °C
HDT at 1.82 MPa	ASTM D648	73 °C

Hardness	Norm	Typical Values
Shore D	ASTM D2240	80

¹⁾ Determined with TA-Instrument DHR rheometer, cone/plate, diameter 60 mm, shear rate 100 s⁻¹

The data contained in this publication are based on our current knowledge and experience. In view of the many factors that may affect processing and application of our product, these data do not relieve processors from carrying out their own investigations and tests; neither do these data imply any guarantee of certain properties, nor the suitability of the product for a specific purpose. Any descriptions, drawings, photographs, data, proportions, weights etc. given herein may change without prior information and do not constitute the agreed contractual quality of the product. It is the responsibility of the recipient of our products to ensure that any proprietary rights and existing laws and legislation are observed. The safety data given in this publication is for information purposes only and does not constitute a legally binding MSDS. The relevant MSDS can be obtained upon request from your supplier or you may contact BASF 3D Printing Solutions GmbH directly at sales@basf-3dps.com. Version 1.2

BASF 3D Printing Solutions GmbH
sales@basf-3dps.com
www.forward-am.com
Photocentric

 UK - Cambridge House, Oxney Road, Peterborough, PE1 5YW. +44 1733 349937. info@photocentric.co.uk

 USA - 2205 West Parkside Lane, Phoenix, 85027, AZ. (623) 581-3220. info@photocentricusa.com
www.photocentricgroup.com